

# From Concept to Production

Our objective is to help you free up time to focus on your research and production. We commit to delivering innovative product and service solutions helping you deliver innovation and ensure quality.

#### Choice and convenience has its benefits

Our portfolio is optimised to help you achieve your mission; innovative products that enable you to develop the solutions your customers demand. A depth of portfolio that will ensure your mission to provide quality products is achieved.

# Create

Fisher Scientific with its access to market leading expertise is the ideal partner on your journey

# **Improve**

Continuous improvement and innovation with a flexible partner able to meet your needs.

#### **Control**

Maintain quality with an efficient supplier partner able to help you manage costs and optimise logistics.

### Test

All you need to run your lab tests and experiments; from biotechnology to chemical synthesis.

# Your partners from concept to production

fisher scientific

An extensive range with custom supply capability for the chemicals, biologics and materials you need.

Scale up

### **Produce**

Portable and at line equipment to monitor your experiments.

Safety equipment backed by our team of specialists to ensure your people and processes are looked after.

#### We will help you to ...

- A Access information and expertise
- C Comply with standards
- H Have the safety equipment you need
- Implement cost savings and efficiencies
- E Enable logistics
- V Validate the right suppliers to meet your needs
- E Ensure security of supply and compliance support



2



# Your bio-materials and chemicals

#### **PAGE 6-7**

Instruments and consumables for the development of your chemicals and materials of biological origin.

Explore our workflow solutions for Cell Biology, Molecular Biology, Protein Biology and Microbiology

Your organic /inorganic materials and chemicals

#### **PAGE 8-9**

Our reaction equipment and control ensures all elements are in place for successful development and laboratory scale production of materials and chemicals



#### **PAGE 16**

Range of sampling devices from solids, liquids, gases and automated systems. Inert, pre-conditioned and specialist products available to meet your application requirements



Your partner from concept to production

# Physical & chemical characterisation

#### **PAGE 10-11**

Successful research and quality control alike require tools that enable understanding of a product. Fisher Scientific can bring an abundance of tools to measure critical product parameters



#### **PAGE 14-15**

A wealth of expertise and a portfolio to match. Ensure your safety needs are met from the laboratory to production floor with one supplier

- PPE

# Chemical compounds, biologics, and elements

#### **PAGE 12-13**

All you need for your product in development, pilot or production delivered as you need it. Our custom capabilities enable the delivery to be customised from product to package






### Your bio-materials and chemicals

#### Supporting the white biotechnology expansion

Fisher Scientific is your one source for the world's greatest life science brands and innovative products. Helping you develop the use of cells such as micro-organisms, or components of cells like enzymes, to generate industrially useful products in sectors such as chemicals, food and feed, detergents, paper and pulp, textiles and biofuels.



Unrivalled

**Cell Biology** Focus on Cell Culture

Quality for bioprocessing is crucial right from the start. That's why we're focused on working with you to optimise your upstream processes like cell culture, and simplify your operations.

#### Leading brands

Gibco & Invitrogen, GE Healthcare Life Sciences & Hyclone, Corning, Fisher BioReagents, Thermo Scientific, Thermo Scientific Biolite, Menzel & Nunc, Fisherbrand, Wheaton Science Products



Organic /inorganic materials and chemicals page 8-9

Physical &

page 10-11

Chemical compounds, biologics, and elements page 12-13

collection equipment & facilities safet shipping and page 14-15

storage page 16

Unrivalled

# **Molecular Biology**

Focus on PCR/qPCR

PCR (polymerase chain reaction) is an invaluable tool for molecular biology. A wide array of applications are supported such as cloning, gene expression analysis, genotyping, sequencing, and mutagenesis. We offer products to help you achieve PCR success for virtually any application. With trusted Applied Biosystems thermal cyclers and real-time PCR systems, industry-leading Invitrogen SuperScript and Platinum Taq enzymes, and millions of reliable Applied Biosystems TagMan Assays, you'll find everything you need to help you achieve PCR success.

ABI Applied Biosystems & Invitrogen, GE Healthcare Lifes Sciences, Fisher BioReagents, Thermo Scientific, Fisherbrand, Eppendorf



Unrivalled

# **Microbiology**

Focus on QA testing

Sampling, sample preparation, inoculation, incubation, identification are all critical steps for your testing. We offer thousands of products to help you.

Leading brands Fisher BioReagents, Thermo Scientific Oxoid, Fisherbrand

Unrivalled

**Protein Biology** 

Focus on PCR/qPCR

Downstream bioprocess is a challenge, that is why we're offering the best on the market: our main brands are putting more than 50 years of experience into protein purification to help you to improve your efficiency (purification columns, antibodies, filtration).

Leading brands

Invitrogen, GE Healthcare Life Science & Whatman, Fisher BioReagents, Thermo Scientific, Fisherbrand





























### Your organic / inorganic materials and chemicals

From sample preparation to synthesis; the equipment, consumables and chemicals all under one supplier.



# Sample preparation

Product type	Brand
Digestion (Kjeldahl)	Velp, Büchi
Filtration and extraction (SPE, nitrogen, protein, phenol, fibre, fat.)	Thermo Scientific, GE Healthcare Whatman, Merck Millipore, Sartorius, <b>Fisherbrand</b> , Macherey Nagel, Büchi, Velp
Milling	Fisherbrand
Mixing	Thermo Scientific, Kinematica, Cowie, Retsch, IKA, <b>Fisherbrand</b>
Grinding, homogenising	Retsch, <b>Fisherbrand</b> , Kinematica, Sonics
With cryogenic options	Thermo Scientific, Kinematica, Sonics, Retsch, IKA, <b>Fisherbrand</b>
Evaporation	Thermo Scientific, Büchi, Heidolph, Cole Parmer, <b>Fisherbrand</b>
Temperature	Ebro, <b>Fisherbrand</b>

#### **thermo**scientific

#### Thermo Scientific™ HAAKE™ Viscotester™ iQ rheometer

Discover the efficiencies you can get in a Quality Control workflow with the Thermo Scientific™ HAAKE™ Viscotester™ iQ rheometer

Quickly adapt the HAAKE Viscotester iQ rheometer to your specific needs with predefined measuring routines, automated software control for SOPs, and much more

Compact yet powerful the HAAKE Viscotester iQ rheometer is a versatile instrument that increases productivity for single viscosity or advanced rheological tests







Physical & chemical characterisation

page IO-II

compounds, biologics, and elements

page 12-13

protective equipment & facilities safet refer to page 14-15

Sample collection, shipping and storage



# Organic and inorganic synthesis

,			
	Product type	Brand	
	Water baths, ultrasonic baths	Memmert, Julabo, Clifton, Fisherbrand	
	Thermostatic baths	Thermo Scientific, Huber, Julabo, Fisherbrand	
	Incubators, shaking incubators	Thermo Scientific, Memmert, Binder	
	Ovens	Thermo Scientific, Memmert, Binder	
	Muffle and tube furnaces	Thermo Scientific, Nabertherm	
	Heating mantles, dry baths	Electrothermal, Fisherbrand	
	Hotplate, hotplate stirrers	Thermo Scientific, Stuart, <b>Fisherbrand</b> , IKA , Heidolph	
	Chiller baths	Thermo Scientific, Huber, Julabo, Fisherbrand	
	Refrigerators, freezers	Thermo Scientific, Liebherr,	
	Ice makers, refrigerant	Scotsman, Sonoco ThermoSafe	
	Dewar flasks	Thermo Scientific	
	Refrigerant circulating baths	Thermo Scientific, Huber, Julabo, Fisherbrand	
	Environmental chambers	Thermo Scientific, Binder, Memmert	/
	Chemical hoods and fume extractors	Thermo Scientific, Erlab	
	Timers and thermometers	Ebro, <b>Fisherbrand</b>	
		/	



# Product optimisation

	Product type	Brand	
	Reaction glassware	Duran, Pyrex	l
	Fittings	Cole Parmer, Buerkle	
/	Distillation: glassware, heating equipment, rotary evaporators	Thermo Scientific, Duran, Pyrex, Cole Parmer, <b>Fisherbrand</b> , Büchi, Heidolph	
	Crystallisation: petri dishes, filtration, boiling and cooling equipment	Thermo Scientific, Duran, Pyrex, GE Healthcare Whatman, Merck Millipore, Sartorius, <b>Fisherbrand</b>	
	Solvent extraction	Velp, Büchi	



## Physical and chemical characterisation

From quality control to research and development choose from a market leading range of testing solutions. Our wealth of technical expertise enables you to maximise your return on investment and ensure your product's performance

Organic / Inorganic chemicals refer to

page 8-9

characterisation

page 10-11

compounds, biologics, and elements

page 12-13

equipment & facilities safety page 14-15

shipping and

collection

page 16

#### **PHYSICAL**



## **CHEMICAL**



# **Micro properties**

**Macro properties** 

Kinematica, Fisherbrand

Mitutoyo, Fisherbrand

IKA, Mitutoyo, Mecmesin

Retsch, Fisherbrand

Lovibond, Cole Parmer, Hach, Fisherbrand

Testo, Ebro Electronic, Fisherbrand

**Brand** 

Mecmesin

Mecmesin

**Product type** 

Consistency

Thickness-gauge

Shore hardness

Scratch testers

Force gauge

Particle size

Colorimetry

Temperature monitoring

Product type	Brand
Anemometers, flowmeters	Thermo Scientific, Aalborg, Bel Art, Burkle, Draeger, Gilmont, <b>Fisherbrand</b>
Dropping point	Cole Parmer Stuart, Mettler Toledo
Melting point	Bibby Stuart , Büchi
Microscopy	Carl Zeiss, Motic, Vision Engeneering (only FR), Olympus, Fisherbrar
Weathering	UVP, Day Light Company, Sunnex, <b>Fisherbrand</b>
Photometry	Thermo Scientific, <b>Fisherbrand</b> , Lovibond Tintometer, Orion, Hach

# **Mechanical testing**

Product type	Brand	
Rheology, viscosimetry	Thermo Scientific Haake	
Tensile strength	Mecmesin	
Torque	Thermo Scientific Nalgene, Mecmesin	
Climatic testing	Memmert, Binder	
Texture analysis	Mecmesin	



# **Qualitative testing**

Product type	Brand	/
Density meter	Mettler Toledo, Bel Art, <b>Fisherbrand</b>	
Refractometry	Bellingham & Stanley, Atago	
Polarimetry	Bellingham & Stanley, Medline	
Moisture	Ohaus, Sartorius, <b>Fisherbrand</b>	



Rap	id	testin	g

Product type	Brand
Rapid test pH test strips	Macherey Nagel, <b>Fisherbrand</b>
Portable meters (pH, redox, conductivity) multiparameters, ion selectivity, electrodes	Thermo Scientific Eutech, Thermo Orion, Mettler Toledo, WTW, <b>Fisherbrand</b>
Colorimetric & Titrimetric test strips and kits	WTW, Lovibond, Macherey Nagel, Fisherbrand
NIR	Thermo Scientific
XRD /XRF	Thermo Scientific
RAMAN	Thermo Scientific
Density Meter	Mettler Toledo
Refractometry	Bellingham & Stanley, Atago

# Chemicals, compounds, biologics and elements

Bio-materials and chemicals

Organic / Inorganic
materials and
chemicals
refer to
page 8-9

Physical & chemical characterisation refer to page 10-11

Chemical compounds, biologics, and elements

refer to page 12-13

Personal protective equipment & facilities safety refer to page 14-15

Sample collection, shipping and storage

# Metals & Materials

- Pure elements
- Transition metals
- Alloys
- Carbon
- Single crystals
- Evaporation materials
- Windows and spheres
- Etchants
- Gauzers
- Nano particles
- Rare earth
- Sputtering

Reagecon

# **Catalysts**

- Fuel cells
- Ferrocenes
- Metal scavengers
- Precious metals
- Catalysts

# Life Science

- Cellular & molecular
- Genomics
- Immunology
- Labelling and detection
- Proteomics
- Biomechanicals
- Molecular Sieves
- Biomedical

Broadest - deepest product portfolio in the industry An extensive range of scaleable, standard and customisable solutions backed by support and logistics capability.

# **Standards**

- AA & XRF
- Electrochemistry
- Conductivity
- Chromatography
- Mass spectrometryViscosity
- Plasma

# **Analytical Chemistry**

- Analytical graphite
- Solvents
- Solutions
- Spectroscopy
- Trace analysis
- Titration

# **Chemicals**

- Inorganics
- Organics
- Organometallics
- Solvents

















# Personal protective equipment & facilities safety


Eye, face and head protection

# Hearing protection

roduct type	Brand
ar plugs, ear muffs	3M, Honeywell

# **Protective** clothing

<b>Product type</b>	Brand
Protective clothing reusable	Kimberly Clark, <b>Fisherbrand</b>
Protective clothing single use	3M, Du Pont, Kimberly Clark, <b>Fisherbrand</b>
Chemical resistant clothing	3M, Du Pont, Kimberly Clark, <b>Fisherbrand</b>
Lab coats	Kimberly Clark, <b>Fisherbrand</b>
Sleeves and oversleeves	3M, Du Pont, Kimberly Clark, <b>Fisherbrand</b>



# Respiratory protection

Product type	Brand
Disposable face masks	3M, Du Pont, Honeywell, Kimberly Clark, <b>Fisherbrand</b>
Disposable respiratory protection	3M, Honeywell
Half and full face masks	3M, Honeywell
Supplier air respirators	3M

# Hand protection

	Product type	Brand
	Chemical resistant, coated, cotton and cut resistant gloves	Ansell, Honeywell
	Gloves for glovebox	Ansell
	Heat resistant gloves	Ansell, Honeywell
	Disposable gloves	Ansell, Honeywell, Kimberly Clark, <b>Fisherbrand</b> , Nitritex
	Finger cots	Honeywell /
1		

# **Foot protection**

/	Product type	Brand	\
/	Shoes and boots	Honeywell	1
	Overshoes	Du Pont, Kimberly Clark, <b>Fisherbrand</b> , Pal International	\



Organic / Inorganic page 8-9

page IO-II

Chemical compounds, biologics, and elements page 12-13

page 14-15

collection shipping and

# **Facility safety**

Product type	Brand
Labelling and signs	Brady
Environmental monitoring	Thermo Scientific
First aid kits	3M
Eyewashes and showers	Kimberly Clark
Glove boxes	Plas Labs
Hazardous handling and storage	Asecos, Justrite
Spill control	3M, <b>Fisherbrand</b>
Matting	Fisherbrand, Purus, Texwipe
Wash bottles	Thermo Scientific, Azlon, Bel Art, Fisherbrand
Wipers	Micronova, Contec, Kimberly Clark







# **Controlled** environment products

/		
	Product type	Brand
	Sterile and non-sterile apparel	Du Pont, Kimberly Clark, Nitritex
	Sterile and non-sterile gloves	Du Pont, Kimberly Clark, Nitritex
	Equipment and furniture	Fisherbrand, Micronova, Nitritex
	Housekeeping	Contec, Kimberly Clark, Micronova, Nitritex
	Disinfectants	Contec, Micronova
	Packaging, tubing and bags	Thermo Scientific, Cole Parmer
	Matting	Fisherbrand, Purus, Texwipe
	Swabs and wipers	Micronova, Contec, Kimberly Clark





# Sample collection & shipping

Bio-materials and chemicals

refer to page 6-7

Organic / inorganic materials and chemicals

> refer to page 8-9

Physical & chemical characterisation

refer to page 10-11 Chemical compounds, biologics, and elements


refer to page 12-13 Personal protective equipment & facilities safety

> refer to page 14-15

Sample collection, shipping and storage

refer to page 16

### **Liquid samples**






# Solid samples

Product type	Brand
Spoons	Bel-Art, Gosselin, <b>Fisherbrand</b>
Spatulas	Bel-Art, <b>Fisherbrand</b>
Scrapers	Bürkle, <b>Fisherbrand</b>
Coring	Thermo Scientific, Gosselin, <b>Fisherbrand</b>
Viscous / frozen / aggressive samplers	Bürkle
Samplers with internal storage	Bürkle
Surface samplers	Bürkle
Sterile samplers	Bel-Art
Tamper proof samplers and devices	Bel-Art
Disposable samplers	Bel-Art, Bürkle, <b>Fisherbrand</b>

# Automated sampling

		-
Product type	Brand	
Syringes	Terumo / BD	
Hazardous liquids	Bürkle	
High pressure samplers	Bürkle	
In-line samplers	Bürkle	
Sterile samplers	Bel-Art	7
Tamper proof samplers and devices	Bel-Art	Τ
Disposable samplers	Bel-Art / Bürkle	
Vacuum and peristaltic pumps	Thermo Scientific, Ilmvac, Cole Parmer	
Large volume in-line samplers	Bürkle	



Product type	Brand
Jugs and beakers	Bürkle, <b>Fisherbrand</b>
Bottles aseptic or sterile	Gosselin, <b>Fisherbrand</b>
Bottles wide necked	Thermo Scientific, Bürkle, <b>Fisherbrand</b>
Sprays	Bürkle, <b>Fisherbrand</b>
Containers sterile or aseptic	Gosselin, Bürkle, <b>Fisherbrand</b>
Bags	Gosselin, Bürkle, <b>Fisherbrand</b>
Light filtering bottles, bottles with safety lock	Fisherbrand

**Austria:** +43(0)800-20 88 40 **Belgium:** +32 (0)56 260 260 **Denmark:** +45 70 27 99 20 **Germany:** +49 (0)2304 9325 **Ireland:** +353 (0)1 885 5854 **Italy:** +39 02 950 59 478

Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00

Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303 Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500

© 2018 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at fishersci.com/trademarks.

