



QUALITY PRODUCTS FOR RELIABLE RESULTS



- + COMPLETE RANGE OF PRODUCTS FROM SAMPLING TO AUTOCLAVING STEPS
- + FOOD INDUSTRY DEDICATED PRODUCTS
- + PRODUCT COMPLIANT WITH INTERNATIONAL STANDARD
- + HIGH PRODUCT TRACEABILITY
- + COST & QUALITY EFFECTIVE ALTERNATIVE TO NON-DISPOSABLE PRODUCTS
- + FOOD COMPLIANT RAW MATERIALS



SAMPLING



- To make sampling easier
- To get quality sample
- To ensure samples shipment
- Leakproof containers
- No cross contamination risks
- Sterilized by ionisation (β treatment)
- Product traceability

*

Description	Product code	Color	Height (mm)	Diameter (mm)	Packaging	Sterile β treatment	Raw materials
Dippers with removable handle 40 ml	TAT30-01	Blue	275	30	Single bag	Sterilized	PP
Dippers with removable handle 125 ml	TAT52-01	Blue	275	52	Single bag	Sterilized	PP
Dippers with removable handle 180 ml	TAT53-02	Blue	305	52	Single bag	Sterilized	PP
Dippers with removable handle 90 ml	TAFL1-01	Blue	290	43	Single bag	Sterilized	PP
Small spoon	CUIP-01	White	125	N/A	Single bag	Sterilized	PS
Large spoon	CUIG-01	White	150	N/A	Single bag	Sterilized	PS
Fork	FOUR-01	White	155	N/A	Single bag	Sterilized	PS
Knife	COUT-01	White	175	N/A	Single bag	Sterilized	PS
Multifunction cutlery	CFM-01	White	180	N/A	Single bag	Sterilized	PS
Straight container hinged cap 35 ml	FL35-01	Natural	66	28	Bulk	Aseptic	PP
Straight container hinged cap 45 ml	FL52-03	Blue	85	29	Bulk	Aseptic	PP
Straight container hinged cap 50 ml	FL60-01	Natural	78	31	Bulk	Aseptic	PP
Straight container hinged cap 70 ml	FL70-04	Natural	80	35	Bulk	Aseptic	PP
Straight container hinged cap 90 ml	FL100-01	Natural	80	43	Bulk	Aseptic	PP
Straight container hinged cap 300 ml	FL300-02	Blue	88	75	Bulk	Aseptic	PP
Rack for FL containers	RACFL2-10	White	N/A	N/A	Bulk	N/A	ABS
Straight container snap cap 25 ml	PL25-04	Natural	58	28	Bulk	Aseptic	PP
Straight container snap cap 60 ml	PL60-03	Natural	83	33	100/bag	Sterilized	PP
Conical container snap cap 200 ml	PC200A-03	Natural	88	62	Bulk	Aseptic	PP
Conical container snap cap 400 ml	PC400-09	Natural	100	85	Bulk	Aseptic	PP
Conical container snap cap 1000 ml	PC1000-09	Natural	130	105	Bulk	Aseptic	PP



STORAGE



- Leakproof containers / bottles
- Unbreakable
- Sterilized by ionisation (β treatment)
- Product traceability

*

Description	Product code	Color	Height (mm)	Diameter (mm)	Packaging	Sterile β treatment	Raw materials
Conical container screw cap 125 ml	PC125D-301	Natural	74	58	Single bag	Aseptic	PP
Conical container screw cap 125 ml	PC125D-300	Natural	74	58	Bulk	Sterilized	PP
Conical container screw cap 125 ml	PC125D-01	Natural	74	58	Bulk	Aseptic	PP
Square bottle wide neck 150 ml	LC150A-01	Natural	95	37	Bulk	Aseptic	PEHD
Square bottle wide neck 250 ml	LC250-03	Natural	109	37	Bulk	Aseptic	PEHD
Square bottle wide neck 500 ml	LC540-12	Natural	122	58	Bulk	Aseptic	PEHD
Square bottle wide neck 1000 ml	LC1040-12	Natural	185	58	Bulk	Aseptic	PEHD
Square bottle wide neck 2000 ml	LC2040-12	Natural	230	58	Bulk	Aseptic	PEHD
Square bottle wide neck 2500 ml	LC2500-01	Natural	265	88	Bulk	Aseptic	PEHD
Carrying handle bottle wide neck 2700 ml	F2700-02	Natural	250	70	Bulk	Aseptic	PEHD



GRINDING / HOMOGENIZATION



- Universal bags
- Ideal to have the most homogenous suspension
- Ideal for suspension sampling with pipettes
- Batch number on each filter bag
- Non-woven filter

*

Description	Product code	Color	Height (mm)	Width (mm)	Packaging	Sterile β treatment	Raw materials
Blender bag without filter 80 ml	SM1-01	Natural	150	105	3x60 bags of 25 units	Sterilized	PE
Blender bag without filter 400 ml	SM2-01	Natural	300	180	5x10 bags of 50 units	Sterilized	PE
Blender bag without filter 3500 ml	SM3-01	Natural	510	380	5x4 bags of 25 units	Sterilized	PE
Blender bag with side filter 400 ml	BBAG-03	Natural	300	190	3x20 bags of 25 units	Sterilized	PE
Blender bag with full filter 400 ml	FBAG-03	Natural	300	190	3x20 bags of 25 units	Sterilized	PE
Clip for bags	CLIP-01	Natural	230	N/A	5x4 bags of 50 units	Aseptic	PE



LIQUID TRANSFER



- High precision tools
- Universal measure system graduation
- Product traceability on each bag
- Serological pipette with narrow end
- Coloured hydrophobe plug
- Fibre free single bag
- Non-pyrogenic, non-cytotoxic, non-haemolytic

*

Description		Product code	Length (mm)	Packaging	Sterile β treatment	Raw materials
Graduated pipette 1 ml	●	P1C-01	270	Single bag	Sterile R	PS
Graduated pipette 2 ml	●	P2C-02	270	Single bag	Sterile R	PS
Graduated pipette 5 ml	●	P5C-01	294	Single bag	Sterile R	PS
Graduated pipette 10 ml	●	P10C-03	294	Single bag	Sterile R	PS
Graduated pipette 25 ml	●	P25C-01	297	Single bag	Sterile R	PS
Graduated pipette 50 ml	●	P50C-01	350	Single bag	Sterile R	PS
Transfer pipette 1 ml		PAS1-00	150	10 boxes x 500 units	Sterilized	PE
Transfer pipette 1 ml		PAS1B-01	225	10 boxes x 10 bags of 20 units	Sterilized	PE
Transfer pipette 3 ml		PAS3-00	150	10 boxes x 500 units	Sterilized	PE
Conical tube with skirt screw cap moulded graduations 50 ml		TU50G-019	H114.5 Ø26.9	10 boxes x 50 units	Aseptic	PP
Conical tube screw cap 15 ml		TC15A-03	H118.5 Ø 14.6	20 bags x 25 units	Aseptic	PP
Conical tube screw cap moulded graduations 50 ml		TC50G-09	H114.5 Ø29.2	10 bags x 50 units	Aseptic	PP



INOCULATION



- Complete range of products from stirrer to inoculating loops
- Highly ergonomic
- Precise tool but smooth with the agar
- Sterilized by ionisation (β treatment)
- Traceability on each bag

*

Description	Product code	Color	Length (mm)	Packaging	Sterile β treatment	Raw materials
Flexible inoculating loop spherical extremity 1 μ l	OS1B-03	White	195	Single bag	Sterilized	PS
Flexible inoculating loop spherical extremity 10 μ l	OS10B-01	Blue	195	Single bag	Sterilized	PS
Inoculating loop 1 μ l	OS1-03	Crystal	192	Single bag	Sterilized	PS
Inoculating loop 10 μ l	OS10-01	Blue	194	Single bag	Sterilized	PS
Flexible inoculating loop 1 μ l / 10 μ l	OSM-03	Green	195	Single bag	Sterilized	PS
Stirrer	AGI-06	White	150	5 boxes x 200 bags of 5 units	Sterilized	PS
L form Spreader	ETAR-01	White	148	5 boxes x 40 bags of 25 units	Sterilized	PS
T form Spreader	ETAT-01	Green	150	5 boxes x 100 bags of 5 units	Sterilized	PS



INCUBATION & DISPOSALS



- Wide range of petri dishes
- Leading European manufacturer of Petri dish
- Dedicated production unit under class 100 environment
- Very high quality control of the product

*


Description	Product code	Color	Height (mm)	Diameter (mm)	Packaging	Sterile β treatment	Raw materials
Petri dish \varnothing 90 mm H 14 mm 3 vents	BP93B-15	Natural	14	90	33/bag	Aseptic	PS
Petri dish \varnothing 140 mm H 20 mm 3 vents	BP143-01	Natural	20	140	11/bag	Aseptic	PS
Petri dish \varnothing 65 mm H 14.5 mm 4 vents	BB64-02	Natural	14.5	65	20/bag	Aseptic	PS
Petri dish \varnothing 90 mm H 16.2 mm 3 vents	BH93B-12	Natural	16.2	90	28/bag	Aseptic	PS



- The safer way of autoclaving your contaminated products
- Wide range of volume (from 0.3L to 33L)
- Quality products
- Product traceability

*

Description	Product code	Printed	Height (mm)	Width (mm)	Packaging	Thermal resistance	Raw materials
Autoclavable bag 9 L 40 μ m	SA09-01	N/A	500	300	Bulk	134°C	PP
Autoclavable bag 9 L 40 μ m biohazard logo	SA09-05	Yes	500	300	30 rolls x 25 units	121°C	PEHD



PLASTIC STRENGTH COMPARED TO GLASS BOTTLES

- + NO AUTOCLAVING STEPS
- + NO WASHING STEPS
- + NO BREAKING RISKS / NO RISK FOR INJURY
- + LIGHTER FOR SHIPMENT
- + SAMPLE TRACEABILITY
- + STERILITY CERTIFICATE ON EACH CASE
- + COST EFFECTIVE
- + TIME SAVING AND MONEY SAVING / RISKS DECREASE

* Please note that the products listed are a small selection from our range, please do not hesitate to contact us for any other requirements.




123 ROUTE DE CAESTRE - BORRE
59529 HAZEBROUCK CEDEX - FRANCE

TÉL. +33 (0)3 28 41 93 03
FAX. +33 (0)3 28 49 56 92
info@gosselin.eu

www.gosselin.eu

Official dealer :



© 2017 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at fishersci.com/trademarks.

Austria: +43(0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20
Germany: +49 (0)2304 9325 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478
Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00
Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303
Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500

 **fisher**scientific
by Thermo Fisher Scientific