

# Azlon®

REUSABLE PLASTIC LABWARE



Focus on  
**Automotive**

# Automotive

## Introduction

For more than half a century, the Azlon® name has been synonymous with high quality plasticware. Available in a variety of polymers including LDPE, PP and HDPE, Azlon® products provide excellent resistance to most oils, fuels and paint\*.

Azlon® reusable plastics cover a broad range of applications in the production environment, offering more than 700 products, including bottles, wash bottles, measuring cylinders, jugs and beakers.



### Wash Bottles

*Azlon®*

- Patented Driplok vapour venting valve prevents solvent drip.
- Available for a variety of solvents.
- Includes new GHS symbols, NFPA diamond, risk phrases and safety information.
- Multilingual and available in 10 languages.



### Aspirators, Carboys and Jerrycans

*Azlon®*

- Available in HDPE and/or PP.
- Sizes ranging from 5l to 50l.
- Ideal for storage and dispensing of large volumes.



### Industrial Scoops

*Azlon®*

- Composed of rigid PE.
- Lightweight.

## Beakers and Measuring Cylinders

Azlon®

- Suitable for both approximate and accurate liquid measurement (Class A and B).
- Available in PP and PMP for glass-like clarity.
- Squat form design for increased stability.



## Storage and Dispensing Bottles

Azlon®

- Available in PP, LDPE and HDPE.
- Wide and narrow neck.
- Spouted cap can be cut to adjust flow rate.
- Pivot nozzle retracts into cap to seal bottle.



## Industrial Funnels

Azlon®

- Composed of rigid PE.
- Unbreakable in normal use.
- Feature straight-sided upper rims to prevent spillage.



\*Polymer compatibility is based on our current knowledge and experience at temperatures of 20°C. In view of the many factors that may affect processing and application, the user should carry out their own tests and experiments to confirm suitability.





SciLabware

**Austria:** +43(0)800-20 88 40 **Belgium:** +32 (0)56 260 260 **Denmark:** +45 70 27 99 20  
**Germany:** +49 (0)2304 9325 **Ireland:** +353 (0)1 885 5854 **Italy:** +39 02 950 59 478  
**Finland:** +358 (0)9 8027 6280 **France:** +33 (0)3 88 67 14 14 **Netherlands:** +31 (0)20 487 70 00  
**Norway:** +47 22 95 59 59 **Portugal:** +351 21 425 33 50 **Spain:** +34 902 239 303  
**Sweden:** +46 31 352 32 00 **Switzerland:** +41 (0)56 618 41 11 **UK:** +44 (0)1509 555 500

© 2018 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [fishersci.com/trademarks](https://fishersci.com/trademarks).

 **fisher scientific**  
part of Thermo Fisher Scientific