fisherbrand favourites
2018/2019
FOR THE LOVE of SCIENCE
fisherbrand
new lab start-up programme
Set Your Lab in Motion
fisher scientific
part of Thermo Fisher Scientific



Redeeming your voucher is **EASY!**

Place orders on your New Lab Start-Up account number

Remember you have one year to reach the thresholds for Fisherbrand vouchers since joining the New Lab Start-Up programme

Once your account passes the required spend thresholds contact your Account Manager or Customer Services and we email you your Fisherbrand Vouchers valid for six months

Redeem your voucher online at

eu.fishersci.com/go/nlsu

Spend **NOK 200 000** receive a further **NOK 5 000 Fisherbrand voucher**

Spend **NOK 100 000** receive a further **NOK 5 000 Fisherbrand voucher**

Spend **NOK 20 000** receive a **NOK 5 000 Fisherbrand voucher**

We have selected some of our top selling Fisherbrand consumable items so you can really make the most out of your Fisherbrand voucher.

Autoclave accessories	3
Cell culture	4-5
Centrifugation	6-7
Cryogenics	8
Filtration	9
Glass & plasticware	10-13
Liquid handling	14-16
Microscopy	17
pH testing	18
Safety	19-20
Sampling & storage	21
Thermometers & timers	22
Weighing accessories	23

Each threshold entitles you to a €500 Fisherbrand voucher to redeem against Fisherbrand consumables items at list price

BAGS, BIOHAZARD, POLYPROPYLENE, AUTOCLAVABLE, HIGH TEMPERATURE

fisherbrand

- For high temperature sterilisation (134°C) to a maximum of 140°C
- All bags are 40µm thick
- The bags should be loosely tied at the top leaving a small hole prior to being autoclaved using autoclave indicator tape
- Opening along width
- Available plain or preprinted with biohazard warnings

Cat. No	Width, mm	Length, mm	Pack qty
Printed polypropylene			
11600312	310	660	100
11553342	410	630	100
11563342	620	780	100
Plain polypropylene			
11583342	410	630	100
11593342	620	780	100

1

1. Apply

Complete the online application form to receive your New Lab Start-Up account number

2

2. Order

Place your orders on this account number. Simply order, or obtain a quotation for your specific requirements

3

3. Redeem

Once your account passes the required spend thresholds contact your Account Manager or Customer Services and we email you your Fisherbrand Vouchers to redeem online.

fisherbrand Focus on Fisherbrand

for all your **glassware** needs

For full range refer to www.eu.fishersci.com/go/fisherbrand

fisherscientific

CELL STRAINERS

fisherbrand

- Sterile, rapid, easy to use device for isolating primary cells to consistently obtain a uniform single-cell suspension from tissues
- Polypropylene frame with nylon mesh
- Sterile
- Individually packed
- Fits 50mL conical tubes

Cell strainers are made of a strong nylon mesh available in three mesh sizes, 40µm, 70µm, and 100µm, for optimal performance in a variety of applications including stem cells and primary cells. Fisherbrand cell strainers provide a fast, simple alternative to gauze filtration when dissociating cells from clumps or primary tissues.

Cat. No	Mesh size, µm	Pack qty
11587522	40	50
11597522	70	50
11517532	100	50

MEDIA BOTTLES, PETG

fisherbrand

- Reduce the risk of cross contamination with these sterile, disposable media bottles
- An inexpensive and shatterproof alternative to glass media bottles
- Nonpyrogenic and noncytotoxic to protect cells
- Moulded-in graduations will not rub off
- Made from clear, lightweight, polyethylene terephthalate copolyester (PETG) providing impact resistance and excellent gas-barrier properties
- Closure is high density polyethylene (HDPE)
- Bottles packed in a shrink-wrapped tray to stay clean
- Heat-shrink band around cap and bottle neck provides visual assurance of sterility for individual bottles until band is removed

Cat. No	Capacity, mL	Pack qty
12074118	125	24
12084118	250	24
12064118	500	12
12094118	1000	12

ERLENMEYER FLASKS, BOROSILICATE GLASS 3.3 NARROW NECK

fisherbrand

Constructed from borosilicate glass. Fisherbrand™ narrow neck conical borosilicate glass Erlenmeyer flasks are graduated and available in a variety of sizes.

Cat. No	Capacity, mL	Certification	Pack qty
Narrow neck			
15499093	50	DIN ISO 1773	10
15409103	100	DIN ISO 1773	10
15419103	200	DIN ISO 1773	10
15429103	250	DIN ISO 1773	10
15439103	500	DIN ISO 1773	10
15449103	1000	DIN ISO 1773	10
15459103	2000	DIN ISO 1773	1
15469103	3000	DIN ISO 1773	1
15479103	5000	DIN ISO 1773	1

TUBE RACKS, MICROCENTRIFUGE, POLYPROPYLENE, PCR

fisherbrand

- Sturdy polypropylene racks ideal for pre or post-PCR sampling applications
- With removable hinged lid accommodates individual 0.2mL tubes or strips of 8 or 12 tubes
- Tube wells are easily identified with imprinted numbers and letters
- Dimensions (l x w x h), mm: 130 x 98 x 33
- Autoclavable

Cat. No	Type	Pack qty
11710344	96 well PCR rack, assorted colours (blue, green, pink, yellow and orange)	5

CELL SPREADERS, L-SHAPED, STERILE

fisherbrand

- For even inoculation of bacterial cultures
- Disposable
- Smooth spreading surface with slight upward angle reduces risk of damaging agar
- L-shape allows access to entire Petri dish or plate surface
- Presterilised blue polypropylene eliminates the need for flaming or autoclaving

Cat. No	Length, mm	Sterility	Colour	Inner pack qty	Pack qty
15625467	145	Yes	Blue	1	100
15615467	145	Yes	Blue	10	500

CELL SPREADERS, TRIANGULAR, STERILE

fisherbrand



- Use 30mm wide spreaders for prepared biplates; 60mm for 100 to 150mm prepared plates
- Autoclavable
- Sterile and individually wrapped

Nonbreakable and reusable polypropylene spreaders available in two sizes with 30 and 60mm bar widths.

Cat. No	Bar width, mm	Colour	Pack qty
15635467	30	Blue	25
15645467	60	Yellow	25

Spend **NOK 200 000** receive a further **NOK 5 000 Fisherbrand voucher**

Spend **NOK 100 000** receive a further **NOK 5 000 Fisherbrand voucher**

Spend **NOK 20 000** receive a **NOK 5 000 Fisherbrand voucher**

ECOUNT™ COLONY COUNTER

fisherbrand

- Electronic counter combined with a Sharpie pen for marking Petri dishes to prevent missing or double counting colonies
- Save battery life
- Verify each count with either beep or LED flash
- First count up, then count down to verify accuracy
- Display the total of all counts (up to 32 separate counts)
- Keep up to 32 separate counts in memory
- Disable counter so you can write totals and notes
- Includes one fine-point Sharpie pen and weighted stand

Combines a multi-function electronic counter with a Sharpie™ pen for marking to prevent missing of double-counting colonies. The Fisherbrand™ eCount™ colony counter has a light, ergonomic body that is balanced for easy manipulation. Different coloured markers can be easily changed for marking versatility.

Cat. No	Length, mm	Pack qty
15253305	190	1

fisherbrand Focus on Fisherbrand

for all your **filtration** needs

For full range refer to www.eu.fishersci.com/go/fisherbrand

fisher scientific

TUBES, MICROCENTRIFUGE GRADUATED

fisherbrand

- Flat caps
- DNase, RNase free
- Autoclavable
- Use between -80°C to 120°C
- Polypropylene
- Colour: natural

Cat. No	Capacity, mL	Pack qty
Standard tubes		
11916955	0.6	500
11926955	1.5	500
11393613	2	500
Low retention tubes		
11996955	0.6	500
11986955	1.5	250
11906965	2	250

TUBES, MICROCENTRIFUGE WITH LOCKING SNAP CAP

fisherbrand

- Graduated, natural polypropylene (PP)
- Non-sterile
- Flat and pierceable cap
- Locking lid to secure the sample and avoid inadvertent opening
- Marking area
- Autoclavable and can withstand temperatures to -86°C
- DNase/RNase and pyrogen free

Convenient, pierceable locking lids snap into place with one-handed operation.

Cat. No	Capacity, mL	Bottom Shape	Diameter, mm	Length, mm	Max. rcf (xg)	Pack qty
15422545	0.5	Conical	10	30	30	500
15432545	1.5	Conical	13	39	26	500
15442545	2.0	Round	13	40	25	500

MICROCENTRIFUGE TUBES WITH SAFELOCK™ LOCKING LID

fisherbrand

- Flat cap
- DNase, RNase free
- Polypropylene
- Autoclavable

Cat. No	Capacity, mL	Max. RCF, xg	Colour	Pack qty
11976955	0.6	30k	Natural	1000
11966955	1.5	26k	Mixed	500
11706467	1.5	26k	Natural	500
11956955	2	25k	Natural	500

TUBES, CENTRIFUGE, 15ML AND 50ML

fisherbrand

- Graduated in 0.5mL subdivisions (15mL) or 5mL subdivisions (50mL)
- Sterile where indicated
- Bulk or racked packs

Cat. No	Pack type	Material	Cap	Max. rcf, xg	Sterile	Dia. x H, mm	Pack qty
15mL							
11755075	Bulk	PP	Flat top	6000	Yes	17 x 119	500
11765075	Bulk	PP	Plug seal	6000	Yes	17 x 119	500
50mL							
11512303	Bulk	PP	Flat top	9400	Yes	29 x 114	500
11809650	Bulk	PP	Plug seal	9400	Yes	29 x 114	500
11829650	Bulk	PP	Plug seal	9400	No	29 x 114	500
15mL							
11879640	Rack	PET	Plug seal	1800	Yes	17 x 119	500
11849650	Rack	PP	Flat top	6000	Yes	17 x 119	500
11889640	Rack	PP	Plug seal	6000	Yes	17 x 119	500
50mL							
11839650	Rack	PET	Plug seal	1800	Yes	29 x 114	500
11819650	Rack	PP	Flat top	9400	Yes	29 x 114	500
11899640	Rack	PP	Plug seal	9400	Yes	29 x 114	500

TUBE RACKS, MICROCENTRIFUGE, POLYPROPYLENE, FOUR-WAY

fisherbrand

These four-way heavy duty racks feature a unique system of tabs and slots, which when linked together, create a larger rack.

Cat. No	Colour	Pack qty
11700055	Assorted (blue, green, pink, yellow and orange)	5

TUBE RACKS, MICROCENTRIFUGE, POLYPROPYLENE, 80 WELL

fisherbrand

Polypropylene 80 well microtube racks ideal for freezer storage.

Cat. No	Colour	Pack qty
11728084	Assorted	5

TUBE RACKS, ADAPT-A-RACK™

fisherbrand

- Each slot adapts to accommodate 5 to 50mL tubes sizes and holds them in a firm upright position
- Made from POM (polyacetal)
- Racks can be linked together for additional holding capacity
- Open sides allow for label viewing
- Flat base to hold tubes upright
- Linked racks should be supported underneath when carrying
- Available in a solid or a combination of colours for easy coding identification
- Autoclavable

Cat. No	Accommodates	Wells	Colour	Overall dimensions, mm (l x w x d)	Well diameter, mm	Pack qty
15300370	5 to 50mL tubes	4	Blue/ green	181 x 56 x 76	12 to 30	2
15320370	5 to 50mL tubes	4	Blue/ yellow	181 x 56 x 76	12 to 30	2
15330370	5 to 50mL tubes	4	Pink/white	181 x 56 x 76	12 to 30	2
15340370	5 to 50mL tubes	4	Blue/blue	181 x 56 x 76	12 to 30	2
15350370	5 to 50mL tubes	4	White/ white	181 x 56 x 76	12 to 30	2
15360370	5 to 50mL tubes	4	Pink/pink	181 x 56 x 76	12 to 30	2
15380370	5 to 50mL tubes	4	Yellow/ yellow	181 x 56 x 76	12 to 30	2
15390370	5 to 50mL tubes	4	Green/ green	181 x 56 x 76	12 to 30	2

fisherbrand Focus on Fisherbrand

for all your **liquid handling** needs

For full range refer to www.eu.fishersci.com/go/fisherbrand

fisher scientific

TEST TUBE RACKS, POM, FULL AND HALF SIZE

fisherbrand

- Made from Delrin™ fibreglass-reinforced polyoxymethylene (POM)
- Tough and more highly resistant to acids, bases, solvents and heat
- Offers the highest chemical and heat resistance (-40°C to +140°C)
- Available in half and full rack sizes for five different tube diameters
- Moulded in a single, continuous piece so no assembly required
- Autoclavable

Cat. No	Tubes	Wells	L x W x H, mm	Well Diam, mm	Colour	Pack qty
Full size						
15340390	10 to 18mL	40	100 x 252 x 83	20	White	1
15310400	15 to 50mL	24	110 x 282 x 85	30	White	1
12327629	5 to 30mL	40	100 x 252 x 83	20	Blue	1
10257963	15 to 50mL	24	110 x 282 x 85	30	Blue	1
15350390	10 to 18mL	40	100 x 252 x 83	20	Green	1
15330400	15 to 50mL	24	110 x 282 x 85	30	Green	1
15360390	10 to 18mL	40	100 x 252 x 83	20	Magenta	1
15350400	15 to 50mL	24	110 x 282 x 85	30	Magenta	1
15360400	15 to 50mL	24	110 x 282 x 85	30	Yellow	1
Half size						
15330430	15 to 50mL	9	110 x 110 x 85	30	White	1
15340420	10 to 18mL	20	100 x 127 x 83	20	Blue	1
15300430	10 to 18mL	16	120 x 122 x 92	25	Blue	1
12317629	15 to 50mL	9	110 x 110 x 85	30	Blue	1
15350420	10 to 18mL	20	100 x 127 x 83	20	Green	1
15340430	15 to 50mL	9	110 x 110 x 85	30	Green	1
15370420	10 to 18mL	20	100 x 127 x 83	20	Magenta	1

1

1. Apply

Complete the online application form to receive your New Lab Start-Up account number

2

2. Order

Place your orders on this account number. Simply order, or obtain a quotation for your specific requirements

3

3. Redeem

Once your account passes the required spend thresholds contact your Account Manager or Customer Services and we email you your Fisherbrand Vouchers to redeem online.

CRYOGENIC STORAGE BOXES, POLYPROPYLENE, WITH GRID INSERTS

fisherbrand

- Autoclavable, temperature resistant from -90°C to +121°C
- High quality polypropylene
- 81 places, 9 x 9 grid, numerically coded
- Robust hinge with safe snap-on lid

For sample storage and transportation.

Cat. No	Colour	Accommodates	Pack qty
Dimensions (l x w x h), 133mm x 133mm x 52mm, 81 place, 9 x 9 grid			
11856893	Natural	81 x 1.2mL to 2.0mL vials	5
11826903	Yellow	81 x 1.2mL to 2.0mL vials	5
11836903	Red	81 x 1.2mL to 2.0mL vials	5
11856903	Blue	81 x 1.2mL to 2.0mL vials	5
Dimensions (l x w x h), 133mm x 133mm x 75mm, 81 place, 9 x 9 grid			
11866903	Natural	81 x 3.0mL to 5.0mL vials	5
11876903	Yellow	81 x 3.0mL to 5.0mL vials	5
11886903	Red	81 x 3.0mL to 5.0mL vials	5
11896903	Green	81 x 3.0mL to 5.0mL vials	5
11806913	Blue	81 x 3.0mL to 5.0mL vials	5

VIALS, CRYOGENIC STORAGE, EXTERNAL THREAD

fisherbrand



- Sterile; not autoclavable
- Noncytotoxic, nonpyrogenic
- Large white writing area
- Graduations in 0.5mL increments
- Use with Fisherbrand colour coders for easier sample identification
- Conical-style
- High density polyethylene
- Self-standing
- Vials are for research use only; not for in vitro diagnosis or parenterals
- Suitable for storage of biological materials in mechanical freezers or in the vapour phase of liquid nitrogen
- CE marked

Externally threaded polypropylene vials with HDPE closures for aseptic technique.

Cat. No	Capacity, mL	Thread Style	Pack qty
11777939	1.2	External	100
11787939	2	External	100
11797939	5	External	50

CRYOBOXES, POLYPROPYLENE, FLAT-PACK CORRUGATED

fisherbrand

- Cryoboxes are supplied flat-pack to eliminate the inconvenience of stacking and reduces the amount of space needed for storage
- Boxes fit in standard freezer racks
- Easy to assemble
- More durable than cardboard boxes as they are not susceptible to moisture
- Significantly reduces the chance of mould
- Dividers included with the boxes
- Store down to temperatures of -80°C

Cat. No	Accommo-dates	Colour	Dimensions, mm (l x w x h)	Wells	Well diam., mm	Pack qty
15316528	0.2mL tubes	Natural	133 x 130 x 30	144	7.9	10

fisherbrand Focus on Fisherbrand

for all your **weighing** needs

For full range refer to
www.eu.fishersci.com/go/fisherbrand

fisherscientific

FILTER PAPERS, CELLULOSE AND GLASS MICROFIBRE

fisherbrand

A range of cellulose and glass fibre filter papers from Fisherbrand

Cat. No	Disc diameter, mm	Pack qty
Grade 113 Cellulose Medium Filtering Qualitative Filter Papers		
11704273	240	100
Grade 601 Cellulose General Purpose Filter Papers		
11576873	110	100
11435248	150	100
Grade 259 Microglass Fibre Filters		
11465238	90	100
11774073	124	100
Grade 261 Microglass Fibre Filters		
11532083	70	100
11734083	125	100
Grade 13 Ashless Medium Filtering Quantitative Filter Papers		
11708963	125	100
11718963	150	100
Grade 1101 Cellulose Filter Papers		
11789975	330	100

EXTRACTION THIMBLES, GRADE 7

fisherbrand

- Made from 100% high pure cotton linters fibres
- For extraction of free lipids in food
- For extraction of sulphur from gases
- For lacquer and binder analysis in paint colours

Suitable for all extractor systems, these thimbles offer high mechanical strength with excellent retention capacity. They are made with high purity cellulose fibres, and are pH neutral and fat free.

Cat. No	Dimensions (d x l), mm	Pack qty
11774043	26 x 60	25

SYRINGES, PLASTIC DISPOSABLE, LUER LOCK OR LUER SLIP

fisherbrand

- Plastic disposable syringes for general laboratory use
- Graduated
- Range of capacities available
- Luer lock or Luer slip fittings

Cat. No	Volume, mL	Pack qty
Luer lock		
12981021	2	100
12901031	5	100
12921031	10	100
12941031	20	100
Luer slip		
12991021	2	100
12911031	5	100
12931031	10	100
12951031	20	100

SYRINGE FILTERS

fisherbrand

- High sample throughput
- Sterile and non-sterile options
- Polypropylene housing - strong and chemically resistant
- Suitable for a broad range of applications

Cat. No	Membrane Material	Pore size, µm	Diameter, mm	Sterile	Pack qty
15206869	PES	0.2	33	Yes	50
15216869	PES	0.45	33	Yes	50
15121499	Nylon	0.2	25	No	50
15131499	Nylon	0.45	25	No	50
15161499	PTFE	0.2	13	No	100
15171499	PTFE	0.45	13	No	100
15141499	PTFE	0.2	25	No	50
15151499	PTFE	0.45	25	No	50
15181499	PVDF	0.2	33	Yes	50
15191499	PVDF	0.45	33	Yes	50
15181489	Hydrophilic PTFE	0.2	25	No	50
15101499	Hydrophilic PTFE	0.45	25	No	50

BEAKERS, SQUAT FORM BOROSILICATE GLASS 3.3

fisherbrand

- With spout
- Graduated
- ISO 3819 DIN 12331

Cat. No	Volume, mL	Exterior diameter, mm	Height, mm	Pack qty
15469073	25	34	25	10
15479073	50	42	60	10
15489073	100	50	70	10
15499073	150	60	80	10
15409083	250	70	95	10
15419083	400	80	110	10
15429083	600	90	125	10
15439083	800	100	135	10
15459083	2000	130	185	1
15469083	3000	150	210	1
15479083	5000	170	270	1
15489083	10000	217	350	1

BEAKERS, POLYPROPYLENE, TRI-CORNERED

fisherbrand

- Suitable for use with commonly used acids, alkalis and solvents
- Each beaker has three drip-free pouring spouts
- Moulded graduations, stackable

Cat. No	Capacity, mL	Height, mm	O.D., mm	Subdivisions, mL	Pack qty
11769398	250	90	76	10	100
11759398	100	72	58	10	100
11799398	1000	145	115	50	100

BOTTLES, REAGENT AND MEDIA, CLEAR BOROSILICATE, WIDE SCREW NECK

fisherbrand

- Graduated and supplied with blue polypropylene cap and pouring ring
- ISO/GL 45 screw thread standard to all sizes, conforms to ISO R1115 and DIN 168
- Chemically resistant and can be repeatedly sterilised to 140°C
- Autoclavable (but do not autoclave bottles with a tightly screwed cap)
- Internal neck diameter 27mm

Cat. No	Capacity, mL	Wall thickness, mm	O.D., mm	Height, mm (bottle only)	Pack qty
15446113	100	1.5	56	100	10
15456113	250	1.5	70	138	10
15476113	500	1.5	86	176	10
15486113	1000	1.7	101	225	10
15406123	2000	2.0	136	260	1
15416123	5000	2.0	181	330	1
15436123	10000	2.7	227	410	1

BURETTES, BOROSILICATE GLASS

fisherbrand

- Constructed of borosilicate glass
- Single bore, with interchangeable PTFE or glass stopcock
- Blue ceramic graduations at 0.10mL
- BS-ISO 385 compliance

Complies with BS-IS 385 standards. These Fisherbrand™ borosilicate glass Class A and Class B burettes include a single bore interchangeable glass or PTFE stopcock. Blue ceramic graduations make volume assessment easy.

Cat. No	Description	Pack qty
Class A burettes		
10450893	Capacity 25mL with PTFE tap	1
10738081	Capacity 50mL with PTFE tap	1
Class B burettes		
10448972	Capacity 50mL with glass tap	1
10569771	Capacity 50mL with PTFE tap	1
Accessories		
12967730	Spare burette tip, glass	5

CUVETTE, QUARTZ, SEMI-MICRO, UV

fisherbrand

- Reduce your reagent use with these semi-micro cells
- Quartz windows for transmission from far ultraviolet through the infrared
- Includes PTFE lid

Cat. No	Capacity, µL	Wavelength range, nm	Pathlength, mm	Internal width, mm	Pack qty
15226033	1000	200 to 2500	10	4	2

CUVETTES, VISIBLE, POLYSTYRENE MACRO & SEMI-MICRO

fisherbrand

- Transparency approximately 90% between 400nm and 800nm
- Material: polystyrene
- Pathlength 10mm
- Wavelength range 336nm to 850nm
- Disposable

Cat. No	Capacity, µL	Dimensions (w x d), mm	Pack qty
11547692	1600	12.5 x 45	100
11847832	1600	12.5 x 45	1000
11537692	4000	12.5 x 45	100
11837832	4000	12.5 x 45	1000

JERRYCANS, NARROW NECK

fisherbrand

- Integrally moulded handle
- Tamper evident screw caps
- Range of capacities

Translucent polyethylene jerrycans with polyethylene closures.

Cat. No	Capacity, L	Height, mm	Neck O.D., mm	Pack qty
11597433	1	165	38	1
11507443	2.5	205	45	1
11517443	5	282	38	1
11527443	10	314	61	1
11537443	25	470	61	1

CARBOYS, HDPE AND POLYPROPYLENE

fisherbrand

- Durable construction for long life
- Choice of materials: HDPE for general use or autoclavable polypropylene
- Space saving rectangular design
- With spigot taps
- These carboys are ideal for storing and dispensing lab water and reagents

Cat. No	Capacity, L	Pack qty
HDPE		
13438039	9	1
13408039	20	1
Polypropylene		
13418039	9	1
13428039	20	1

CYLINDERS, BOROSILICATE GLASS, CLASS B

fisherbrand

- Graduated in blue ceramic markings
- Hexagonal base
- Individual reorder code on each item
- DIN 12680 BS 604 ISO 4788
- Pouring spout

Class B cylinders are ideal for basic measurement of liquids in qualitative work such as measuring solvents for reactions, making up solutions or adding an excess of a reagent, and are ideal for schools, universities and for general research laboratories.

Cat. No	Capacity, mL	Graduations, mL	Pack qty
11507702	5	0.1	2
11517702	10	0.2	2
11527702	25	0.5	2
11537702	50	1	2
11547702	100	1	2
11557702	250	2	2
11567702	500	5	2
11577702	1000	10	2

CYLINDERS, PPCO AND PMP, GRADUATED WITH SPOUT

fisherbrand

- Large rounded bases ribbed for reinforcement and stability
- Calibrated 'To Contain/To Deliver' at 20°C - meets ASTM laboratory standards
- Chemical, heat and impact resistant makes these cylinders excellent for long term use
- No meniscus to confuse readings, thereby eliminating guesswork

Cat. No	Capacity, mL	Pack qty
Cylinders, PPCO		
11947884	10	12
11957884	25	12
11967884	50	12
11997874	100	8
11907884	250	8
11967874	500	6
11937874	1000	4
11927874	2000	2
Cylinders, PMP		
11907894	25	18
11917894	50	18
11977884	100	12
11917884	500	8
11977874	1000	6
11947874	2000	4

CONICAL SEPARATING FUNNELS, BOROSILICATE GLASS, WITH PTFE STOPCOCK ISO 4800

fisherbrand

- Available with either interchangeable PTFE stopcock or glass stopcock in the wider product portfolio
- Supplied with a glass and plastic stopper

Cat. No	Capacity, mL	Stopper size	Pack qty
PTFE stopcock, interchangeable			
11572782	100	19/26	1
11582782	250	24/29	1

VOLUMETRIC FLASKS, CLEAR BOROSILICATE CLASS A CERTIFIED

fisherbrand

- ISO 1042, DIN 12664
- One mark graduation
- Interchangeable polyethylene stopper
- Details on each flask include confirmation of compliance to International Standards as well as an individual reorder code
- Batch certificate available

Cat. No	Capacity, mL	Tolerance, mL	Stopper Ø, mm	Neck O.D., mm	Pack qty
Flasks, clear, white markings					
11576923	5	0.04	10/19	13	5
11586923	10	0.04	10/19	13	5
11596923	20	0.04	10/19	13	5
11506933	25	0.04	10/19	13	5
11516933	50	0.06	12/21	15	5
11526933	100	0.10	12/21	15	5
11536933	200	0.20	14/23	17	2
11546933	250	0.30	14/23	17	2
11556933	500	0.25	19/24	22	2
11566933	1000	0.40	24/29	28	2
11576933	2000	0.60	29/32	28	1

WASHBOTTLES, WIDE NECK LDPE SAFETY-LABELLED AND COLOUR CODED

fisherbrand

- For leakproof dispensing of your most common solvents
- Easy to read LDPE solvent-resistant printed bottles
- Colour coded and preprinted with a selection of different common solvent types for easy identification

Cat. No	Label	Capacity, mL	Closure colour	Pack qty
11592463	Acetone	500	Red	6
11582463	Acetone	1000	Red	6
11532473	Deionised water	500	Blue	6
11562463	Distilled Water	500	Blue	6
11512473	Isopropanol	500	Yellow	6
11502473	Methanol	500	Green	6
11522473	Toluene	500	Red	6
11572463	Water	500	Blue	6

WASHBOTTLES, LDPE, ROUND, WIDE NECK, VENTING, SOLVENT LABELLED

fisherbrand

- Labelled and colour coded for some of the most commonly used solvents
- Unique patented two piece venting assembly prevents build up of solvents within the bottle, eliminating solvent drips from the spout due to internal evaporation
- LDPE bottle with polypropylene closures and venting assembly
- Only use with solvents compatible with LDPE

Cat. No	Capacity, mL	Label	Closure colour	Pack qty
11567153	500	Acetone	Red	3
12368616	500	Ethanol	Natural	3
11587153	500	Isopropanol	Yellow	3
11577153	500	Methanol	Green	3
11507163	500	DIY/custom	Natural	3

WASHBOTTLES, LDPE, WIDE NECK, VENTING, LABELLED, RIGHT-TO-KNOW

fisherbrand

- Pre-printed with chemical name and formula, NFPA section 704 four colour diamond, health hazard, CAS number and suggested protective clothing and equipment
- Wide neck for easy refilling
- Vented to prevent pressure build up, eliminating solvent drips
- Valve allows solvent to be dispensed in both an upright or inverted position
- Leakproof
- Translucent with colour coded polypropylene closures

Cat. No	Capacity, mL	Label	Closure colour	Pack qty
11938485	1000	Acetone	Red	4
12369195	500	Ethanol	Natural	6
12309205	500	Isopropanol	Yellow	6
12319205	500	Methanol	Green	6
12359195	500	Assorted pack	Assorted	6

WASHBOTTLES, NARROW NECK LDPE

fisherbrand

- Translucent white wash bottles delivering a single drop or fine stream
- Manufactured from LDPE with a one-piece polypropylene screw cap and nozzle
- Tip may be cut back to increase flow

Basic wash bottles for general laboratory use.

Cat. No	Capacity, mL	Pack qty
11532463	250	6
11542463	500	6

fisherbrand Focus on Fisherbrand

for all your **glassware** needs

For full range refer to
www.eu.fishersci.com/go/fisherbrand

fisherscientific

PIPETTES, PASTEUR, GLASS

fisherbrand

- Unplugged
- Soda lime glass
- For general laboratory use

Soda lime glass open point pipettes.

Cat. No	Length, mm	Pack qty
11546963	150	1000
11566963	230	1000
11755108	270	1000

PIPETTES, TRANSFER

fisherbrand

- Low density polyethylene
- Transparent
- Graduated or non-graduated
- Sterile options available
- Various packaging formats

Cat. No	Type	Sterile	Length, mm	Drop volume, µL	Drop per mL	Pack qty
13469118	Transfer pipette PE, 1mL	No	104	33	30	400
13499108	Transfer pipette PE, 1mL, graduated	No	150	33	30	500
13439118	Transfer pipette PE, 1mL, graduated, extended tip	No	150	33	30	500
13489108	Transfer pipette PE, 1mL, graduated	Yes	150	33	30	500
13419118	Transfer pipette PE, 1mL, graduated, inner pack of 10	Yes	150	33	30	500
13429118	Transfer pipette PE, 1mL, graduated, inner pack of 20	Yes	150	33	30	500
13439108	Transfer pipette PE, 3mL, graduated	No	155	40	25	500
13469108	Transfer pipette PE, 3mL, graduated	Yes	155	40	25	500
13479108	Transfer pipette PE, 3mL, graduated, inner pack of 10	Yes	155	40	25	500
13409118	Transfer pipette PE, 3mL, graduated, inner pack of 20	Yes	155	40	25	500
13459118	Transfer pipette PE, 4mL, thin stem	No	150	33	30	500
13459108	Transfer pipette PE, 4mL	No	150	33	50	500
13449108	Transfer pipette PE, 7mL, extra long	No	300	50	20	100
13449118	Transfer pipette PE, 10mL, jumbo	No	170	56	18	200

PIPETTES, SEROLOGICAL, POLYSTYRENE

fisherbrand

- A black magnifier stripe runs lengthwise along the pipette making the meniscus obvious and reducing reading errors
- 5mL, 10mL, 25mL and 50mL sizes have both ascending and descending graduations
- Tip design on the 25mL and 50mL sizes increases the effect of surface tension to minimise dripping
- Bulk packed or individually wrapped plastic/plastic or paper/plastic

Cat. No	Colour	Capacity, mL	Graduations, mL	Pack qty
Pipettes, individually wrapped plastic/plastic				
11819660	Yellow	1	0.01	1000
11879650	Green	2	0.01	500
11829660	Blue	5	0.1	200
11839660	Orange	10	0.1	200
11517752	Red	25	0.2	200
11537752	Purple	50	0.5	100
Pipettes, individually wrapped paper/plastic				
11849181	Yellow	1	0.01	1000
11859181	Green	2	0.01	500
11869181	Blue	5	0.1	200
11879181	Orange	10	0.1	200
11839181	Red	25	0.5	200
11889181	Purple	50	0.5	100
Bulk packed				
11879660	Yellow	1	0.01	1000
11889660	Green	2	0.01	500
11899660	Blue	5	0.1	500
11809670	Orange	10	0.1	500

PIPETTE CONTROLLER FILLER

fisherbrand

- Works with both glass and plastic pipettes from 0.1 to 100mL
- Blow-out bulb for use with blow-out pipettes
- Hydrophobic membrane filter reduces penetration by liquids
- Allows aspiration up to 50mL with one compression
- Fill rate is continuously variable with the pipetting lever
- Lever provides simple discharge
- Valve system is designed so flow rate does not affect accuracy
- Chemical-resistant
- Autoclavable

Durable and reliable large-capacity controller limits over-aspiration

Cat. No	Pack qty
15219805	1

UNIVERSAL PIPETTE PUMPS

fisherbrand

- Made from high-grade polyethylene
- Accepts both glass and serological pipettes
- Ideal for soap and acid titrations
- Clear markings make measuring easy
- The 10mL pump is marked in 0.10mL increments
- The 25mL pump is marked in 0.20mL increments
- Rotating thumbwheel draws or dispensed liquid
- Side lever allows entire contents to be rapidly dispensed
- 25mL pump fits both 10mL and 25mL pipettes

Easy one-hand operation provides accurate titration

Cat. No	Type	Pack qty
15209805	Blue 2mL	1
15239805	Green 10mL	1
15229805	Red 25mL	1

PIPETTORS, VARIABLE SINGLE AND MULTI CHANNEL, ELITE™

fisherbrand

- Classic single and multi-channel, manual adjustable pipettors
- Available in a range of dispensing volume ranges
- Ergonomically designed, comfortable pipetting
- Low pipetting and tip ejection forces reducing RSI risks
- Autoclavable at 121°C (20 min) without disassembly
- Optimal fit with Fisherbrand SureOne™ pipettor tips

Cat. No	Volume, µL	Pack qty
Single channel		
11815762	0.2 to 2	1
11825762	0.5 to 5	1
11835762	1.0 to 10	1
11845762	2 to 20	1
11855762	5 to 50	1
11865762	10 to 100	1
11875762	20 to 200	1
11885762	100 to 1000	1
Eight channel		
11815772	1 to 10	1
11835772	5 to 50	1
11825772	10 to 100	1

ELITE™ PIPETTOR STAND

fisherbrand

- Accommodates up to six Elite™ pipettors
- Also suitable for most other commonly-used models
- Sturdy and freestanding on the bench
- Durable grey plastic

Cat. No	Pack qty
11895772	1

PIPETTING REAGENT RESERVOIRS

fisherbrand

- Disposable reagent reservoirs for use with multichannel pipettors
- Clear PVC
- Non-sterile

Cat. No	Description	Pack qty
12369175	Pipetting reservoir, non-sterile, PVC, disposable, clear, 50mL	100

Spend **NOK 200 000** receive a further **NOK 5 000 Fisherbrand voucher**

Spend **NOK 100 000** receive a further **NOK 5 000 Fisherbrand voucher**

Spend **NOK 20 000** receive a **NOK 5 000 Fisherbrand voucher**

SUREONE™ PIPETTOR TIPS

fisherbrand

- Compatible with most popular brands of pipettor
- SureOne™ achieves optimal fit with Fisherbrand™ Elite™ pipettors
- Non-sterile products - certified to be free of RNase/DNase and DNA
- Sterile products - e-beam sterile products are certified to be free of RNase/DNase, pyrogen, bioburden, PCR inhibitors and endotoxins
- Filter tip options also available
- Autoclavable

Fisherbrand™ SureOne™ pipettor tips are a comprehensive line of universal fit pipettor tips, available in a range of volumes and styles, from 5µL to 10mL, in bulk, racked, sterile racked and the environmentally friendly reload system.

Cat. No	Pack type	Pack qty
Nano micropoint tips 5µL, graduated at 2.5µL		
11987724	Bulk clear	1000
11997724	Racked clear	960
11907734	Racked sterile clear	960
11997714	Filter sterile reload clear	960
Standard micropoint tips 10µL, graduated at 2µL		
11933416	Bulk clear	1000
11953416	Racked clear	960
10053014	Racked sterile clear	960
11973416	Reload clear	960
11903466	Filter sterile clear	960
11907724	Filter sterile reload clear	960
Extended length micropoint tip 10µL, graduated at 2.5µL		
11983416	Bulk clear	1000
11588402	Racked clear	960
10527014	Racked sterile clear	960
11967714	Reload clear	960
11913466	Filter sterile clear	960
11917724	Filter sterile reload clear	960
Universal bevelled tip 20µL		
11933426	Filter sterile clear	1000
11937724	Filter sterile reload clear	960
Universal bevelled tip 100µL		
11953466	Filter sterile clear	960
11947724	Filter sterile reload clear	960
Universal bevelled tip 200µL		
10678325	Racked clear	960
11963426	Racked sterile clear	960
11578412	Reload clear	960
10124314	Bulk yellow	1000
11983426	Racked yellow	960
11903436	Racked sterile yellow	960
11913436	Reload yellow	960

Cat. No	Pack type	Pack qty
Universal thin wall micropoint tip 200µL		
11538422	Bulk clear	1000
11933436	Racked clear	960
11943436	Racked sterile clear	960
11953436	Reload clear	960
11963436	Bulk yellow	1000
11973436	Racked yellow	960
11983436	Racked sterile yellow	960
11993436	Reload yellow	960
Universal bevelled tip 200µL, graduated at 10µL, 50µL and 100µL		
11943446	Bulk clear	1000
11953446	Racked clear	960
11963446	Racked sterile clear	960
12922521	Reload clear	960
11903446	Bulk yellow	1000
11913446	Racked yellow	960
11923446	Racked sterile yellow	960
11933446	Reload yellow	960
Universal micropoint tip 200µL, graduated at 10µL, 50µL and 100µL		
11957724	Filter sterile reload clear	960
Universal bevelled tip 300µL, graduated at 10µL, 50µL, 100µL and 200µL		
11993446	Bulk clear	1000
11903456	Racked clear	960
Universal micropoint tip 300µL, graduated at 10µL, 50µL, 100µL and 200µL		
10003414	Racked sterile clear	960
11538442	Reload clear	960
Universal micropoint tip, 1000µL, graduated at 100µL, 200µL, 500µL and 1000µL		
11973466	Filter sterile clear	960
11977724	Filter sterile reload clear	560
Universal micropoint tip 1250µL, graduated at 100µL, 200µL, 500µL, 1000µL		
11548442	Bulk clear	1000
11568442	Racked clear	960
10164694	Racked sterile clear	960
11588442	Reload clear	960
11963466	Filter bulk clear	960
10778535	Bulk blue	1000
10537014	Racked blue	960
10492725	Racked sterile blue	960
11963456	Reload blue	960

COVER SLIPS, BOROSILICATE GLASS

fisherbrand

- Manufactured from clear white borosilicate glass
- Square or rectangular shape
- Available in a variety of other shapes and sizes and thicknesses in the wider product portfolio
- Packed in plastic boxes to prevent breakage

Cat. No	Dimensions, mm	Pack qty
No. 1 Square, 0.13mm to 0.17mm thick		
12333128	22 x 22	200
No. 1 Rectangular, 0.13mm to 0.17mm thick		
11348503	24 x 32	100

MICROSCOPE SLIDES

fisherbrand

- Dimensions 76mm x 26mm
- Available plain or twin frosted
- Ground on all four edges
- Wrapped in cellophane for improved cleanliness

Washed and polished glass slides with 90° ground edges.

Cat. No	Thickness, mm	Pack qty
Plain		
12373118	0.8 to 1	50
12383118	1.0 to 1.2	50
Twin frost		
11562203	0.8 to 1	50
11572203	1.0 to 1.2	50

MICROSCOPE SLIDE BOXES

fisherbrand

- Moulded, rigid boxes securely hold standard microscope slides in grooved slots
- Boxes hold 25 to 100 standard slides
- Slots and lining are numbered to correspond to slide inventory sheet
- Variety of lid closure types
- Stackable cases include feet for maximum stability

Cat. No	Capacity, Slides	Colour	Closure Type	Liner Material	Material	Pack qty
11741476	25	Blue	Hinged lid	Unlined	PP	1
11771476	100	Blue	Hinged lid	Unlined	PP	1
11781476	100	Red	Hinged lid	Unlined	PP	1
11791476	100	White	Hinged lid	Unlined	PP	1
11701486	100	Blue	Nickel plated clasp	Foam lined	ABS	1

fisherbrand Focus on Fisherbrand

for all your **Traceable™ Products**

For full range refer to
www.eu.fishersci.com/go/fisherbrand

fisherscientific

PH INDICATOR PAPER, REELS, UNIVERSAL

fisherbrand

- Filter paper strips impregnated with colour pH indicators
- Papers in the full product portfolio cover several ranges between pH 0 and pH 14
- Handy reference chart on the packs shows colour changes in steps of pH 2
- Supplied as dispenser reels each 5m x 7mm (l x w)

Provides rapid and precise readings. Fisherbrand™ universal pH indicator papers include a colour scale printed on the cover for convenience.

Cat. No	pH range	Pack qty
10482341	1 to 14	4

PH INDICATOR PAPER, STICKS

fisherbrand

- Sticks with different indicator papers sealed onto each strip
- Non-bleeding
- Supplied with a colour comparison chart
- Dimensions 85mm x 6mm
- The sticks are sufficiently long to avoid contact between the fingers and the test sample

Cat. No	pH range	Pack qty
10018080	0.0 to 6.0	100
10642751	0.0 to 14.0	100
10353641	3.6 to 6.1	100
10333501	4.5 to 10.0	100
10271751	7.0 to 14.0	100

STARCH-IODIDE INDICATOR PAPER

fisherbrand

- Indicator strips for strong oxidising agents like chlorine gas and nitrites
- Impregnated with starch-potassium iodide
- Colour change white to blue

Cat. No	Width, mm	Length, mm	Pack qty
11592413	10	60	200

fisherbrand Focus on Fisherbrand

for all your **weighing** needs

For full range refer to
www.eu.fishersci.com/go/fisherbrand

fisherscientific

GLOVES, EXAMINATION, COMFORT NITRILE

fisherbrand

- Gloves with enhanced comfort and with tactile sensitivity
- Exceptional fit, feel and durability
- Ideal for everyday protection in the lab
- Blue nitrile
- Ambidextrous with beaded rolled cuffs and with textured fingers
- Thickness: 0.07mm (palm), 0.09mm (finger)
- Length 241.3mm
- Powder-free and latex free
- Non-sterile
- Disposable

Cat. No	Size	Length, mm	Pack qty
15622367	XS	241	200
15632367	S	241	200
15642367	M	241	200
15652367	L	241	200
15662367	XL	241	180

GLOVES, EXAMINATION, EXTENDED CUFF, NITRILE

fisherbrand

- Gloves with exceptional durability and added protection
- These extended cuff nitrile gloves are also extra-thick
- Powder free, latex free
- Fully textured finish for a superior wet or dry grip
- Ambidextrous and non-sterile with beaded cuff
- Thickness: 0.15mm (palm), 0.18mm (finger)
- Extra long at 305mm
- Colour: teal green
- Conforms to EN ISO 374/Type B

Cat. No	Size	Length, mm	Pack qty
15612367	XS	305	50
15662357	S	305	50
15672357	M	305	50
15682357	L	305	50
15692357	XL	305	50

WIRE GLOVE BOX HOLDERS

fisherbrand

- Epoxy coated steel wire rack
- Dimensions (d x w x h) interior: one box holder 108mm x 140mm x 208mm; three box holder 108mm x 250mm x 454mm
- Wall mounting screws included

Epoxy coated steel wire racks which hold most major brands of glove boxes. Available as a single box holder or the three box holder in the full product portfolio.

Cat. No	Type	Pack qty
11895843	Three box holder	1

LABORATORY COATS, POLYCOTTON WASHABLE, UNISEX

fisherbrand

- Colour: white or blue in the full product portfolio
- Length: 132cm
- Material 65% polyester/35% cotton
- Three pockets

Manufactured from a quality pre-shrunk polycotton fabric, these smart, traditional lab coats are suitable for industrial laundering at temperatures up to 85°C. Features include: two lower patch pockets, breast pocket with integral pen pocket, concealed stud fastened front, single rear vent for ease of movement. Not CE marked.

Cat. No	Size	Pack qty
White		
11558102	S	1
11568102	M	1
11578102	L	1
11588102	XL	1
11598102	2XL	1
11508112	3XL	1

LABORATORY COATS, DISPOSABLE, POLYPROPYLENE

fisherbrand

- Latex-free spunbond polypropylene construction
- Disposable
- Comfortable and lightweight
- Ideal for laboratory or workplace visitors
- Elastic cuffs hold sleeves in place
- Five snaps for a secure closure
- Standard collar
- No pockets
- Fabric weight: 50g/m²

Cat. No	Size	Pack qty
White		
15431922	S	25
15441922	M	25
15451922	L	25
15461922	XL	25
15471922	2XL	25
15481922	3XL	25

FACEMASKS, DISPOSABLE

fisherbrand

- Disposable, single use
- Choice of ear loops or tie closure
- Non-woven polypropylene outer layer
- Thermally bonded non-woven polypropylene inner layer
- Latex-free
- Choice of blue or white
- Universal size/fit

Provides advanced protection

Cat. No	Type	Thickness	Pack qty
15451932	Disposable face mask with ear loops, white	2-ply	500
15461932	Disposable face mask with ear loops, blue	3-ply	500
15471932	Disposable face mask with ear loops, white	3-ply	500
15481932	Disposable face mask with tie closure, blue	3-ply	500

SHOE COVERS, DISPOSABLE

fisherbrand

- Protect against dirt, grime and certain dry particulates
- Single-use universal fit
- Blue
- Polypropylene, with elasticated tops
- Latex-free
- With or without anti-skid sole

Spunbond polypropylene shoe covers

Cat. No	Type	Size	Colour	Pack qty
15401952	Shoe cover with anti-skid	Universal	Blue	300
15481942	Shoe cover without anti-skid	Universal	Blue	300
15411952	Shoe cover with anti-skid	X-Large	Blue	300
15491942	Shoe cover without anti-skid	X-Large	Blue	300

fisherbrand Focus on Fisherbrand

for all your **weighing** needs

For full range refer to
www.eu.fishersci.com/go/fisherbrand

fisherscientific

STORAGE SET, MAGLAB™

fisherbrand

- Organise your common lab and office accessories away from your immediate benchtop
- Modular set includes a magnetic rack and four dedicated magnetic storage boxes made from translucent ABS plastic for easy content identification and access
- Each rack features four powerful magnets for a secure hold onto most metal surfaces
- Alternatively, mount on non-metallic surfaces with a self-adhesive metal mounting plate (included)
- MagRack™ box holds four 50mL tubes and nine 15mL tubes
- MagWipe™ box holds a standard (110mm x 210mm) Kimwipes™ box
- MagPette™ box holds two pipettors (fits most popular styles)
- MagBox™ box holds miscellaneous accessories

Create storage space without crowding a limited workspace. The Fisherbrand™ MagLab™ storage set uses magnetic mounting to store miscellaneous lab and office supplies away from the benchtop in four storage units constructed of durable, coloured ABS plastic.

Cat. No	Description	Pack qty
11942581	MagLab™ storage set, including rack and four boxes blue, green, purple, orange, each 522mm x 393mm x 102mm (w x d x h)	1

ALUMINIUM FOIL, ROLL

fisherbrand

- Supplied as rolls
- Packed in individual dispenser boxes with cutter bar
- Thickness 0.018mm
- Also available as heavy-gauge rolls 0.024mm thick offering greater folding strength, good for covering sharp edges (see our website for details)

General purpose foil for sealing, weighing, and transferring samples plus many other laboratory applications.

Cat. No	Dimensions	Pack qty
11769408	60m x 305mm	1

ALUMINIUM FOIL DISPENSER

fisherbrand

- Compact, easily relocated foil dispenser
- Constructed from blue ABS plastic
- Stable with non-slip base
- Safety blade is integrated into the cover
- Accepts most commonly used foil roll sizes
- Dimensions (w x d x h), mm: 190 x 100 x 120

Cat. No	Pack qty
11957994	1

STORAGE TRAY, POLYPROPYLENE, SAMPLES

fisherbrand

- Constructed from corrugated polypropylene
- Moisture resistant, significantly reducing the chance of mould
- Lightweight and sturdy to hold up to 24 full specimen containers
- Stackable with other trays
- Removable dividers allow outer shell to be used for storage or transport of laboratory products
- Supplied flat-packed
- Pack includes: 10 trays and 10 dividers
- Disposable

Cat. No	Compartments	Compartment dimensions, mm	Overall dimensions, mm (l x w x h)	Pack qty
15376548	24	58 x 58	406 x 260 x 89	10

TRANSPORT BOX, POLYCARBONATE

fisherbrand

- Ideal for transporting biological and clinical samples, as well as instruments and products that need to keep clean and dry under testing environmental conditions
- Polycarbonate construction
- Available in three colours
- Silicone water-tight seal and three lid clasps provide secure closure
- Carry handle folds neatly into body space allowing the units to be stacked
- Lid opens a full 180°, allowing total access to contents and making it easier to clean
- Accommodates 13mm and 16mm tubes in a 72 place Delrin rack or similar sized rack
- Use the separators provided to create your own compartment sizes, or use empty to transport large products and equipment
- Autoclavable

Cat. No	Description	Dimensions, (w x d x h), mm	Pack qty
15165564	Clear with blue handle	380 x 196 x 160	1
15175564	Red with red handle	380 x 196 x 160	1
15155564	Yellow with yellow handle	380 x 196 x 160	1

THERMOMETER, STAINLESS STEEL LOLLIPOP PROBE, TRACEABLE™

fisherbrand

- Shockproof and waterproof unit delivers reading updates every second
- One-key operation recalls MIN/MAX temperature results, °C or °F switchable
- Supplied with battery, probe, probe cover with pocket clip, Traceable™ certificate

Cat. No	Temperature range, °C	Resolution	Probe length, mm	Pack qty
11785853	-50 to 300°C	0.1° from -20 to 200°C; or 1°C otherwise	200	1

THERMOMETERS, WHITE BACKED, RED SPIRIT FILLED

fisherbrand

- General purpose/stirring thermometers
- Clear amber graduations
- Reinforced bulb for stirring
- Non-roll fitment on the end
- Filled with red spirit

Cat. No	Length, mm	Range, °C	Subdivisions, °C	Immersion	Pack qty
11561993	305	-10 to 110	1	76mm	1
11587273	305	-20 to 110	1	Total	1

COMBINED THERMOMETER/ CLOCK/HUMIDITY MONITOR, TRACEABLE™

fisherbrand

- Three-function LCD display with large 13mm digits
- Dual switchable ranges: 0° to 50°C (32° to 122°F) accuracy to ±1°C
- Flip-down easel for standing on bench or desktop
- Relative humidity range is 20 to 90%, resolution is 1% RH, and accuracy is ±8%
- Memory recalls highest and lowest temperature and humidity readings
- Clock shows time of day to the minute, with accuracy to 0.0190 seconds
- Includes 1.5V AAA battery, built-in stand and wall mount
- Individually serial-numbered Traceable certificate is included
- Overall dimensions 108mm x 57mm x 13mm

Measures ambient temperature, relative humidity and tells time. These combined thermometer/clock/humidity monitors are designed for easy operation, accuracy and reliability in industrial, educational, hospital and governmental labs and more. They are ideal for use in incubators, storerooms, drying chambers, hoods, cleanrooms, environmental cabinets, plus a wide range of other general lab applications.

Cat. No	Pack qty
11725843	1

FOUR-CHANNEL TIMER, TRACEABLE™

fisherbrand

- Set four separate channels independently from 99 hours, 59 minutes, 59 seconds to one second
- Features: count up/down, time in/out, memories, alarm, 12/24 hour clock
- Large high display allows viewing from a distance
- Remarkable memory returns display to previously programmed countdown time at the touch of a button
- Extra-loud, high decibel alarms for 1 minute or can be silenced manually
- Timing capacity: 99 hours, 59 minutes, 59 seconds
- Resolution 1 second with accuracy of 0.01%
- Supplied with clip, stand, magnet, battery, Traceable™ certificate

Cat. No	Dimensions, mm	Pack qty
11745863	70 x 64 x 13	1

TIMER, MULTICOLOURED, TRACEABLE™

fisherbrand

- Three bright, interchangeable frames with assorted colours supplied with each timer for a distinctive appearance
- Count-up/count-down/alarm/clock functionality on four separate channels
- Memory
- Indicates elapsed time since alarming
- Times up to 99hr, 59min, 59s, with accuracy 0.01% and resolution one second
- Includes Traceable certificate, three assorted brightly-coloured frames, batteries, easel bench stand, magnetic back

Cat. No	Dimensions, mm	Pack qty
11775863	70 x 57 x 13	1

WALL CLOCK, TRACEABLE™

fisherbrand

- Sturdy laboratory wall clock with sweeping second hand
- Clock tells time to the second with 0.01% quartz-crystal accuracy
- Large, easy to read 250mm dial
- Dust and splash resistant case, wall mounting screw, and one AA battery
- Individually serial-numbered Traceable™ certificate is provided

Cat. No	Overall diameter, mm	Pack qty
11719815	305	1

WEIGHING BOATS, POLYSTYRENE, DISPOSABLE

fisherbrand

- Available as standard or anti-static
- Diamond or square shaped
- In black or white
- 5mL to 280mL capacity

Cat. No	Shape	Capacity, mL	Pack qty
Standard black			
12952850	Diamond	5	500
12962850	Diamond	30	500
12972850	Diamond	100	500
12982850	Square	10	500
12992850	Square	85	500
12902860	Square	280	500
Anti-static black			
12912860	Diamond	5	500
12922860	Diamond	30	500
12932860	Diamond	100	500
12942860	Square	10	500
12952860	Square	85	500
12962860	Square	280	500
Standard white			
12932840	Diamond	5	500
11573422	Diamond	30	500
12387552	Diamond	100	500
11593422	Square	10	500
11503432	Square	85	500
11513432	Square	280	500
Anti-static white			
12992840	Diamond	5	500
11533432	Diamond	30	500
11543432	Diamond	100	500
12922850	Square	10	500
11680302	Square	85	500
12608513	Square	280	500

WEIGHING BOATS, DISPOSABLE, PAPER

fisherbrand

- Available in small and medium in both brown for light coloured samples and white for dark samples
- Made from FSC™ Certified (FSC™ Mix) paper (Eco-IN) and when disposed of in the standard waste stream they will naturally biodegrade (Eco-OUT)
- Present a truly green solution to sample weighing
- Control contents like a polystyrene weigh boat
- Easier to handle than regular weighing papers
- Grease-proof paper that meets FDA 21 CFR 176.170 (components of paper in contact with aqueous and fatty foods) and with 2l CFR 176.180 (contact with dry foods)
- Compatible with heat applications with a temperature limit of 210°C

These Fisherbrand™ Mix paper weighboats are an environmentally friendly, easy to use alternative to regular weighing papers.

Cat. No	Size	Pack qty
Brown paper boats		
15422214	Small (35 x 35 x 15.8mm)	500
15432214	Medium (47.6 x 47.6 x 14.2mm)	500
White paper boats		
15408113	Small (35 x 35 x 15.8mm)	500
15442214	Medium (47.6 x 47.6 x 14.2 mm)	500

SPATULABALANCE™, TRACEABLE™

fisherbrand

- Three position soft touch keys in the handle tares (sets to zero), holds (freezes display) and changes grams to ounces
- Balance with LCD digital display is located in the easy-grip handle
- Chemical and corrosion-resistant ABS plastic transfers materials without sticking
- Scoop detaches from balance for dishwasher safe cleaning
- Low battery indicator
- Markings on see-through scoop that comes as standard with the SpatulaBalance™ (Cat.No 15388764) are graduated from 5 to 30mL in 5mL increments for weighing liquids with ease
- Markings on see-through larger volume scoop (Cat. No 15398764) are graduated at 20mL and 40mL
- Weighing range 0.1g to 300g (readability 0.1g)

This unique spatula scoops material and instantly weighs it. Ideal for transfer and weighing of crystals, granulates, solids, liquids, precipitates, chemicals and precious materials.

Cat. No	Pack qty
11744416	1

new lab start-up programme

Set Your Lab in Motion

© 2018 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at fishersci.com/trademarks.

Austria: +43(0)800-20 88 40 **Belgium:** +32 (0)56 260 260 **Denmark:** +45 70 27 99 20
Germany: +49 (0)2304 9325 **Ireland:** +353 (0)1 885 5854 **Italy:** +39 02 950 59 478
Finland: +358 (0)9 8027 6280 **France:** +33 (0)3 88 67 14 14 **Netherlands:** +31 (0)20 487 70 00
Norway: +47 22 95 59 59 **Portugal:** +351 21 425 33 50 **Spain:** +34 902 239 303
Sweden: +46 31 352 32 00 **Switzerland:** +41 (0)56 618 41 11 **UK:** +44 (0)1509 555 500

fisher scientific
part of **Thermo Fisher Scientific**