








Amersham™ ECL™ Western blotting detection reagents

Product	Amersham ECL start	Amersham ECL	Amersham ECL Prime	Amersham ECL Select™	Amersham ECL Plex™
Detection type	Chemiluminescence	Chemiluminescence	Chemiluminescence	Chemiluminescence	Fluorescence
Optimal membrane	Amersham Protran	Amersham Protran	Amersham Hybond™ P Amersham Protran	Amersham Hybond P Amersham Protran	Amersham Hybond LFP Amersham Protran Premium
Recommended detection	Amersham Hyperfilm™ (X-ray film) or ImageQuant™ LAS 500	Amersham Hyperfilm (X-ray film) or ImageQuant LAS 500	Amersham Imager 600 series X-ray film is also an option	Amersham Imager 600 series X-ray film is also an option	Typhoon™ FLA series Amersham Imager 600RGB
Signal duration	< 3 h	< 2 h	< 24 h	< 2 h	> 3 months
Typical applications	<ul style="list-style-type: none">Routine protein detectionHigh expressed proteins e.g house keeping proteinsTagged proteins	<ul style="list-style-type: none">Routine protein detectionProtein confirmationOverexpressed proteinsTagged proteins	<ul style="list-style-type: none">Protein quantitationProtein confirmationProtein regulation and expression analysis	<ul style="list-style-type: none">Protein quantitationProtein confirmationProtein regulation and expression analysis	<ul style="list-style-type: none">Multiplex analysisNormalization to housekeeping proteinAnalysis of post translational modifications and isoforms
Typical results	 <p>WB ERK 1/2; LOD: 320 ng; DR</p>	 <p>WB ERK 1/2; LOD: 40 ng; DR: 2.1</p>	 <p>WB ERK 1/2; LOD: 20 ng; DR: 2.4</p>	 <p>WB ERK 1/2; LOD: 5 ng; DR: 2.4</p>	 <p>WB ERK 1/2 (Cy5 on FLA 9500); LOD 10 ng; DR: 3</p>

Ordering information

Amersham ECL Start	Quantity	Code number
Amersham ECL start Western blotting detection reagent	200 ml for 2000 cm ² membrane	RPN3243
Amersham ECL start Western blotting detection reagent	400 ml for 4000 cm ² membrane	RPN3244

Amersham ECL

Amersham ECL Western blotting detection reagent	100 ml for 1000 cm ² membrane	RPN2109
Amersham ECL Western blotting detection reagent	200 ml for 2000 cm ² membrane	RPN2209
Amersham ECL Western blotting detection reagent	400 ml for 4000 cm ² membrane	RPN2106
Amersham ECL Western blotting detection reagent	600 ml for 6000 cm ² membrane	RPN2134

Amersham ECL Prime

Amersham ECL Prime Western blotting detection reagent	100 ml for 1000 cm ² membrane	RPN2232
Amersham ECL Prime Western blotting detection reagent	300 ml for 3000 cm ² membrane	RPN2236

Amersham ECL Select

Amersham ECL Select Western blotting detection reagent	100 ml for 1000 cm ² membrane	RPN2235
--	--	---------

Amersham ECL Plex

Amersham ECL Plex Combination Pack (includes Cy TM 3, Cy5, Amersham ECL Plex Marker, and Amersham Protran Premium)	For 1000 cm ² membrane	RPN998
Amersham ECL Plex Combination Pack (includes Cy3, Cy5, Amersham ECL Plex Marker, and Amersham Protran Premium)	For 1000 cm ² membrane	RPN999
Amersham ECL Plex goat- α -mouse IgG-Cy2, Cy3, Cy5	For 1000 cm ² or 4000 cm ² membrane	
Amersham ECL Plex goat- α -rabbit IgG-Cy2, Cy3, Cy5	For 1000 cm ² or 4000 cm ² membrane	

Blocking Reagents

Amersham ECL Blocking agent	40 g	RPN2125
Amersham ECL Prime Blocking reagent	40 g	RPN418

Blotting paper	Quantity	Code number
Whatman TM 3MM blotting paper	46 x 57 cm	3030-917

Amersham Western blotting membranes

Amersham Protran 0.2 NC	1 roll, 30 cm x 4 m	10600001
Amersham Protran 0.45 NC	1 roll, 30 cm x 4 m	10600002
Amersham Protran Premium 0.2 NC	1 roll, 30 cm x 4 m	10600004
Amersham Protran Premium 0.45 NC	1 roll, 30 cm x 4 m	10600003
Amersham Hybond P 0.2 PVDF	1 roll, 26 cm x 4 m	10600021
Amersham Hybond P 0.45 PVDF	1 roll, 30 cm x 4 m	10600023
Amersham Hybond LFP 0.2 PVDF	1 roll, 25.4 cm x 4 m	10600022

Molecular weight markers

Amersham ECL DualVue TM Markers – visible on the gel, blot, film, and imager	25 loadings	RPN810
Amersham ECL Rainbow TM Marker-Full range	250 μ l	RPN800E
Amersham ECL Plex Fluorescent Rainbow Marker	120 μ l	RPN850E

Secondary antibodies

Amersham ECL Mouse IgG, HRP-Linked Whole Ab	1 ml	NA931-1ML
Amersham ECL Rabbit IgG, HRP-Linked Whole Ab	1 ml	NA934-1ML

Autoradiography film

Amersham Hyperfilm ECL 5 x 7"	50 sheets	28-9068-35
Amersham Hyperfilm ECL 18 x 24 cm	50 sheets	28-9068-36
Amersham Hyperfilm ECL 8 x 10"	50 sheets	28-9068-38

For more product and pack size information plus additional products, please visit www.gelifesciences.com

These products are available from GE Healthcare distributors www.gelifesciences.com/distributors

GE and GE monogram and are trademarks of General Electric Company. Amersham, Cy, ECL, ECL DualVue, ECL Plex, ECL Select, Hybond, Hyperfilm, ImageQuant, Rainbow, Typhoon, and Whatman are trademarks of General Electric Company or one of its subsidiaries. Amersham ECL start, Amersham ECL Prime and Amersham ECL Select is manufactured and sold under license from Cyanogen Srl and is subject of US Canadian and EU patent application number EP1950207A1, US2008176251A1, ITBO20070037A1, EP1962095A1, US2008241868A1, ITBO20070112A1, together with other equivalent granted patents and patent applications in other countries.

© 2011–2014 General Electric Company – All rights reserved. First published Apr. 2011.

GE Healthcare, Amersham Place, Little Chalfont, Buckinghamshire, HP7 9NA, UK.

28-9960-69 AG 12/2014