

## Corning® 5L Erlenmeyer Flasks

### Efficient scale-up of suspension cultures

The Corning 5L Erlenmeyer flask is designed to help scale-up suspension culture with space efficiency in mind. The flasks are sterile and ready-to-use, ideal for shaker culture applications, and storage.

#### Materials

- ▶ Vessels are constructed from polycarbonate that has been tested and shown to be noncytotoxic. This USP Class VI material provides excellent optical clarity and mechanical strength.
- ▶ Caps are constructed from USP Class VI polypropylene that is free from heavy metals.

#### Features

- ▶ Available with both baffled or plain bottom
- ▶ Molded-in graduations for accuracy
- ▶ Large vent cap for continuous gas exchange while ensuring sterility and preventing leakage
- ▶ Sterility Assurance Level (SAL) of  $10^{-6}$
- ▶ Certified nonpyrogenic and RNase-/DNase-free
- ▶ Erlenmeyer flasks are autoclavable once at 121°C, 15 psi for 20 minutes. Repeated autoclaving weakens the flask and is not recommended. Vent cap is not autoclavable.




## Corning® 5L Erlenmeyer Flasks Ordering Information

Fisher Scientific Cat. No.	Corning Cat. No.	Description	Qty/Pk	Qty/Cs
07-200-926	431684	5L Erlenmeyer flask, vent cap, baffled bottom	1	4
07-200-927	431685	5L Erlenmeyer, vent cap, plain bottom	1	4
07-200-925	431682	Vent cap for 5L Erlenmeyer flasks	1	24



For information on Corning's full range of Erlenmeyer flasks and other scale-up products including Corning HYPERStack® vessels and Corning microcarriers, please visit [www.fishersci.com/corning](http://www.fishersci.com/corning).



[www.corning.com/lifesciences/solutions](http://www.corning.com/lifesciences/solutions)

Corning single-use adhesion and suspension cell culture products enable scale-up in bioprocess manufacturing. From cell line development and process development to GMP manufacturing, our vessels provide the necessary platform to accomplish your goals. Supporting products such as Closed System Solutions, media, and advanced surfaces round out the product offering, providing a complete solution.

**CORNING** | **FALCON** **AXYGEN** **GOSSSELIN** **PYREX**

**Warranty/Disclaimer:** Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For a listing of trademarks, visit us at [www.corning.com/lifesciences/trademarks](http://www.corning.com/lifesciences/trademarks). All other trademarks in this document are the property of their respective owners.

© 2014 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

### In the United States:

For customer service, call 1-800-766-7000  
To fax an order, use 1-800-926-1166  
To order online: [www.fishersci.com](http://www.fishersci.com)

### In Canada:

For customer service, call 1-800-234-7437  
To fax an order, use 1-800-463-2996  
To order online: [www.fishersci.ca](http://www.fishersci.ca)



A Thermo Fisher Scientific Brand

BN0604144