



Thermo Scientific Nunc
Conical Centrifuge Tubes



Innovation
at every turn



Discover

 a suite of conical centrifuge tubes uniquely designed to improve results across your entire cell culture process.

High-volume, Wide-mouth Conical Centrifuge Tube

More volume. More access. More space for decanting.

Thermo Scientific™ Nunc™ 250 mL Conical Tube

The new Thermo Scientific Nunc 250 mL Conical Tube offers added capacity for your larger samples with a one-of-a-kind wide mouth design, providing open, easy access for pipetting, decanting and removal of the pellet following centrifugation.

Easy access for pipetting and simple removal of pellet



Safely and completely decant after centrifugation



One-of-a-kind wide mouth for up to 250 mL capacity



A New Spin on Lower Volume Conical Centrifuge Tubes

Flip or twist. Rack or bulk. Write big or small. You choose.

We offer a variety of options when your research calls for using 15 and 50 mL conical centrifuge tubes in your lab.

Thermo Scientific™ Nunc™ 15 mL and 50 mL Conical Centrifuge Tubes

Increased traceability

- largest writing area on the market provides more space for labeling your research

Environmentally friendly

- recyclable plastic rack reduces waste in the lab
- new plastic rack minimizes risk of contamination and particles
- tubes are sterile with a 10^{-6} SAL

Highly certified

- higher RCF rating enables greater range of applications from low-speed to super-speed centrifugation
- leak-proof to protect your samples
- USP Class VI, non-pyrogenic, non-cytotoxic and RNase/DNase free to help ensure optimal reliability and performance

largest **writing area**
on the market



Thermo Scientific™ Nunc™ EZ Flip™ Conical Centrifuge Tubes

Ergonomic design

- enables one-handed opening and closing

Integrated leak-proof cap

- prevents cross contamination

Optimal performance

- clarified polypropylene combines chemical resistance and high-speed tolerance

Compatible with a wide range of centrifuge rotors

- standard dimensions provide greater usability in your lab

enables **one-handed**
opening and closing



Ordering Information

| Description | | | | | |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|----------------|---------|---------------------|--|
| Thermo Scientific Nunc Conical Centrifuge Tubes are RNase/DNase free, USP Class VI, Sterile 10 ⁻⁶ SAL, Non-pyrogenic, Non-cytotoxic, clarified polypropylene and leak-proof | | | | | |
| Cat No | Volume | Max RCF Tested | Packing | Unit per Pack /Case | |
| 12-566-441 | 250 mL | 10.000* | Bagged | 4/40 | |
| 12-565-268 | 15 mL | 10.500* | Bulk | 50/500 | |
| 12-565-269 | 15 mL | 10.500* | Racked | 25/500 | |
| 12-565-270 | 50 mL | 17.000* | Bulk | 25/500 | |
| 12-565-271 | 50 mL | 17.000* | Racked | 25/300 | |



| Description | | | | | |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|----------------|---------|---------------------|--|
| Thermo Scientific Nunc EZ Flip Conical Centrifuge Tubes are RNase/DNase free, USP Class VI, Sterile 10 ⁻⁶ SAL, Non-pyrogenic, Non-cytotoxic, clarified polypropylene and leak-proof | | | | | |
| Cat No | Volume | Max RCF Tested | Packing | Unit per Pack /Case | |
| 12-565-801 | 15 mL | 8500* | Bulk | 50/500 | |
| 12-565-802 | 15 mL | 8500* | Racked | 50/500 | |
| 12-565-803 | 50 mL | 9500* | Bulk | 25/500 | |
| 12-565-804 | 50 mL | 9500* | Racked | 25/500 | |



*When fully supported by conical rotor cavity or conical adaptor. Note the maximum speeds listed are guidelines only. These speeds have been achieved in reliability tests based on sedimentation of 1.2 specific gravity fluid at 18°C.

All conical centrifuge tubes are made of clarified polypropylene, giving customers good view of separations and final pellet.

All conical centrifuge tubes are for research use only.

Enhance your Centrifuge Experience

Our centrifuge systems deliver outstanding performance and reliability in the lab. From microcentrifuges and benchtop instruments, to advanced floor models and innovative carbon fiber rotors – all are designed to offer exceptional quality for consistent results. To see available centrifuge and rotor solutions, visit us at: thermoscientific.com/centrifugation



© 2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries.



In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca

Thermo
SCIENTIFIC

A Thermo Fisher Scientific Brand